

Expandet Quick Driva and Mini Driva

Expandet Nylon Mini Driva is an effective solution for small and lightweight fixings in plasterboard.

Expandet Metal Quick Driva is an effective solution for fixing of cable tray (max. 3mm) direct on plasterboard.



ADVANTAGES


- Fast and easy fixing of lightweight objects in plasterboards.
- No pre-drilling.


Type	Load capacities
DIMENSION	N_{rec}
	Recommended tension load kN*
Metal Quick Driva	0,03
Nylon Mini Driva	0,03


* Loads are recommended maximum in plasterboards with 100 mm spacing. Numbers in () are only valid for fixing in two layer plasterboard. Safety factor is included (≥ 3). 1 kN \approx 100 kg.

NOTE: Is the recommended spacing not applied the load capacity will be reduced.


INSTALLATION QUICK DRIVA:


- 1]  Mount Quick Driva on screwdriver or bit (PH1). Press Quick Driva against the wall, where the fixture is wanted.


- 2]  Screw Quick Driva flush with the wall. Avoid over-tightening


- 3]  The installation is finished

INSTALLATION MINI DRIVA:

- 1]  Mount Mini Driva on screwdriver or bit (poz. 2). Press Mini Driva against the wall, where the fixture is wanted.

- 2]  Screw Mini Driva flush with the wall. Avoid over-tightening

- 3]  Tighten the screw through the fixture and into the Mini Driva

- 4]  The installation is finished

Expandet Quick Driva and Mini Driva




EXPANDET QUICK DRIVA AND MINI DRIVA

TYPE DIMENSION	THICKNESS OF MATERIAL MM	SCREW DIA. MM	THICKNESS OF FIXTURE (MAX.) MM	EXPANDET ARTICLE NO.	PCS. PER BOX	EAN 13 PER BOX
Metal Quick Driva	9-26		3	961120	200+PH 1 bit	5708620096704
Nylon Mini Driva *	9-13	3,0	12	961011	250	5708620096889

* Supplied with Poz.2 screw

PLASTERBOARD



Quick Driva

Mini Driva